






MANUFACTURED IN IRELAND
 www.csc.ie sales@csc.ie
 Phone: 353 (0)1 835 1311
 Fax: +353 (0)1 835 1580

FUME CUPBOARDS

CHEMFLOW BENCH MOUNTED

DESCRIPTION	CONFIGURATIONS							
 <p>PRODUCT OVERVIEW</p> <p>The Chemflow Bench Mounted fume cupboard is suited to general laboratory use and can be tailored to suit a customer's exact requirements.</p> <p>Manufactured as standard from 6mm thick fabricated sheet PVC. Although we can manufacture from a range of other materials including epoxy painted mild steel and stainless steel, our PVC standard construction offers a much higher chemical resistant longer life fume cupboard.</p> <p>Designed and manufactured to meet and surpass the recommendations' laid down in the BS/EN 14175 fume cupboard standards.</p> <p>Our range of standard sizes is as per the data sheet but our flexibility allows us to meet your exact requirements regarding height, widths and depths of fume cupboard.</p> <p>Our unique energy saving systems can be installed in all of our chemflow fume cupboards.</p> <p>OPTIONAL EXTRAS Chemflow Benched Mounted Fume Cupboards come with the option of Energy Save, Solvent and Acid Storage Units.</p>  	Model	1200	1500	1800	2000	2400	Other	
	External Dimensions (WxHxD)	1200x2375x900	1500x2375x900	1800x2375x900	2000x2375x900	2400x2375x900	2400x2375x900	Ask
	Working Dimensions (WxHxD)	880x1100x720	1180x1100x720	1480x1100x720	1680x1100x720	2080x1100x720	2080x1100x720	Ask
	Outer Skin	6mm PVC	6mm PVC	6mm PVC	6mm PVC	6mm PVC	6mm PVC	
	Linings	Compact Laminate	Compact Laminate	Compact Laminate	Compact Laminate	Compact Laminate	Compact Laminate	
	Lighting	Fluorescent 400/500 lux Spur Switch	Fluorescent 400/500 lux Spur Switch	Fluorescent 400/500 lux Spur Switch	Fluorescent 400/500 lux Spur Switch	Fluorescent 400/500 lux Spur Switch	Fluorescent 400/500 lux Spur Switch	
	Mains Power	220 v 50 hz	220 v 50 hz	220 v 50 hz	220 v 50 hz	220 v 50 hz	220 v 50 hz	
	Twin Electrical Sockets	1	1	2	2	2	2	
	Water	1	1	2	2	2	2	
	Sash	6mm Toughened	6mm Toughened	6mm Toughened	6mm Toughened	6mm Toughened	6mm Toughened	Ask
	Worktop	Trespa Top Lab Plus	Trespa Top Lab Plus	Trespa Top Lab Plus	Trespa Top Lab Plus	Trespa Top Lab Plus	Trespa Top Lab Plus	Optional
	Drip Cup	1 x Vulcathene	1 x Vulcathene	1 x Vulcathene	1 x Vulcathene	1 x Vulcathene	1 x Vulcathene	Ask
	Airflow Monitor	Standard	Standard	Standard	Standard	Standard	Standard	Optional
	Frame	Epoxy Steel	Epoxy Steel	Epoxy Steel	Epoxy Steel	Epoxy Steel	Epoxy Steel	Optional
	AVAILABLE OPTIONS							
	Outer Skin							
Mild Steel	✓	✓	✓	✓	✓	✓		
Stainless Steel	✓	✓	✓	✓	✓	✓		
Polypropylene	✓	✓	✓	✓	✓	✓		
Inner Linings								
PVC	✓	✓	✓	✓	✓	✓		
Polypropylene	✓	✓	✓	✓	✓	✓		
Stainless Steel	✓	✓	✓	✓	✓	✓		
GRP	✓	✓	✓	✓	✓	✓		
Electrical Sockets	✓	✓	✓	✓	✓	✓		
Gas/Water/ Nitrogen	✓	✓	✓	✓	✓	✓		
Ceramic Sink	✓	✓	✓	✓	✓	✓		
PP Sink	✓	✓	✓	✓	✓	✓		
Stainless Sink	✓	✓	✓	✓	✓	✓		
Ceramic Worktop	✓	✓	✓	✓	✓	✓		
Epoxy Resin Worktop	✓	✓	✓	✓	✓	✓		
Steel Steel W.top	✓	✓	✓	✓	✓	✓		
Polypropylene W.top	✓	✓	✓	✓	✓	✓		
Atex rating	✓	✓	✓	✓	✓	✓		
Electrical RCB	✓	✓	✓	✓	✓	✓		
Sockets RCB	✓	✓	✓	✓	✓	✓		
Data Points	✓	✓	✓	✓	✓	✓		
Polycarbonate Sash	✓	✓	✓	✓	✓	✓		



FUME CUPBOARDS

CHEMFLOW BENCH MOUNTED

